

OPSIS LiquidLINE Kjeldahl Consumables

Preparation is the key to good results

OPSIS Brings you Glassware

- European made
- High Precision
- Durable

OPSIS Brings you Catalysts

- European made
- Low Environmental Impact
- Cost Savings



KJELDAHL TABLETS, KT-211/220/230/240/250/260-A

Name	Benefit	Size	Box	Composition	Recommendation
KT-211-A Missouri Tablet, Cu, 0.3%	Recommended. The best mix of Efficiency and Environmental impact	3.5g	1000 tablets	99,7% Potassium Sulphate 0,3% Copper(II) Sulphate 5-hydrate	A popular and universal tablet. Easy to use but low copper content gives slightly longer digestion time. Our Recommended solution for fast, efficient and environment friendly digestion.
KT-220-A Micro Copper, Cu, 9%	Reduced amount of chemicals	1.65g	1000 tablets	91% Potassium Sulphate 9% Copper(II) Sulphate 5-hydrate	Recommended for micro Kjeldahl applications.
KT-230-A Universal Copper, Cu, 9%	Fast, Safe and Efficient	5g	1000 tablets	91% Potassium Sulphate 9% Copper(II) Sulphate 5-hydrate	Our most universal and popular tablet. Good performance and low impact on the environment.
KT-240-A Titanium, Cu-TiO ₂	Saves time at low environmental impact	3.71g	1000 tablets	47,17% Sodium Sulphate 47,17% Potassium Sulphate 2,83% Copper(II) Sulphate 5-hydrate 2,83% Titanium (IV) Oxide	Perfect balance between environment and fast digestion.
KT-250-A Selenium, Se, 0.1%	Fast	3.5g	1000 tablets	99,9% Potassium Sulphate 0,1% Selenium	Fast digestion but not optimal for the environment.
KT-260-A Wieninger, Se-Cu, 2%	Fast according to Wieninger	3.5g	1000 tablets	96,5% Potassium Sulphate 1,5% Copper(II) Sulphate 5-hydrate 2% Selenium	

KJELDAHL TUBES AND GLASSWARE, TU-214/220/221/222-A

Name	Benefit	Size	Box	Dimensions	Recommendation
TU-214-A KjelROC Tubes 250 ml	OP SIS LiquidLINE Quality Glass	250 ml	20 Tubes	Diameter 42 mm Height = 300±2 mm	High Quality Borosilicate Glass. All Tubes with OP SIS LiquidLINE logo
TU-221-A KjelROC Tubes 750 ml	OP SIS LiquidLINE Quality Glass	750 ml	4 Tubes	Height = 300±2 mm	High Quality Borosilicate Glass.
TU-220-A Conical Flask 250 ml	OP SIS LiquidLINE Quality Glass	250 ml	12 flasks	Height = 155 mm	High Quality Borosilicate Glass, Excellent use together with KjelROC Distillation Unit
TU-222-A Boiling Rods	OP SIS LiquidLINE Quality Glass	300 mm	10 rods	Height = 300 mm	High Quality Borosilicate Glass, To be used when digesting water and liquid samples.



TU-214-A



TU-221-A



TU-220-A



TU-222-A

Specifications subject to change without notice

Opsis AB, Box 244
SE-244 02 Furulund Sweden
Telephone +46 46 72 25 00
Telefax +46 46 72 25 01
E-mail info@opsis.se
www.liquidline.se

DASTEC S.R.L.

Representantes / Distribuidores Exclusivos

Argentina

Tel: (+54 11) 5352 2500

Email: info@dastecsr.com.ar

Web: www.dastecsr.com.ar



LP 1004
2016 09

OP SIS
LIQUIDLINE®

OP SIS AB • +46 46 72 25 00 • info@opsis.se • www.liquidline.se